

Technical Information

Product	
Title	NE8FF
Connection Type	Adapter
Gender	female

Electrical	
Contact resistance	< 10 m Ω
Dielectric strength	1 kVdc
Frequencyrange	1 - 100 MHz
Insulation resistance	> 0.5 G Ω
Rated current per contact	1,5 A
Rated voltage	< 50 V
Standard compliance	TIA/EIA 586B, IEC11801

Mechanical	
Insertion force	\leq 20 N
Withdrawal force	\leq 20 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Latch lock

Material	
Contact plating	0.2 µm Au over Ni plating
Contacts	Bronze (CuSn8)
Insert	PBTP 15 % GR
Shell	AlMgSi 0.5, black plated
Strain relief	CuZn35Pb2, Tin plated

Environmental	
Flammability	UL 94 HB
Temperature range	-30 °C to +80 °C