

Cordless hot-melt glue applicator

# MobileGlue 3011

without rechargeable battery and charger  
EAN 4007841 069001  
Article number 069001



Serie 3



Power-For-All  
Alliance (Bosch)

ø 11 mm


Klebesticks

20 g/min

Fördermenge



2 Stufen 130°C /  
200°C



austauschbare Düse



Quick Start 2min



Akku-Laufzeit



Eco-Mode  
(automatisches  
Abschalten)



no memory effect

## Function description

Cordless and powerful bonding for up to 90 minutes. The MG 3011 with 18V Bosch PFA battery system has two temperature settings of 130 °C/200 °C. This is bonding for professionals – portable, flexible and powerful.

## Technical specifications

Temperature	130 – 200 °C
Warm-up time	2 min
Delivery rate	20 gr/min
Max. stick diameter	11 mm
Temperature display	LED segment display
Function, hanger	No
Soft grip	Yes
Idle mode	No
Nozzle can be changed	Yes
Stroke adjustment	No
Temperature, adjustable	Yes
Temperature accuracy +/-	5 °C
Heating element	PTC heating element
Voltage range (min)	18 V

Rechargeable battery run time	up to 90 minutes
Rechargeable battery voltage	18 V
Rechargeable battery capacity	2.5 Ah
Rechargeable battery type	Li-ion
Restart protection	No
Power supply, detail	Rechargeable lithium-ion battery
Suitable for	Rubber, Wood, ceramic, Leather, Metal, Paper, Card / cardboard boxes, Tarpaulins, PP
Melt temperature	130 – 200 °C
Dimensions (L x W x H)	256 x 55 x 178 mm
Version	without rechargeable battery and charger
PU1, net weight	0,35 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841069001
Scope of delivery	incl. 3 glue sticks

<https://www.steinell.de>

Subject to technical modifications

10.2023 Page 1 from 2

Cordless hot-melt glue applicator

# MobileGlue 3011

without rechargeable battery and charger  
EAN 4007841 069001  
Article number 069001



## Accessories

EAN 4007841 006754	Glue sticks Ø 11 mm Crystal
EAN 4007841 006761	Glue sticks, Ø 11 mm Ultra-Power
EAN 4007841 050092	General-purpose glue sticks Ø 11 mm
EAN 4007841 052416	Acrylate glue sticks Ø 11 mm
EAN 4007841 052430	Fast glue sticks Ø 11 mm
EAN 4007841 052423	Flex glue sticks Ø 11 mm
EAN 4007841 052409	Low Melt glue sticks Ø 11 mm
EAN 4007841 064891	Glitter Sticks Ø 11 mm
EAN 4007841 006815	Color sticks Ø 11 mm
EAN 4007841 006778	Glue sticks Ø 11 mm wood
EAN 4007841 006792	Glue sticks Ø 11 mm black