

Hot-melt glue applicator

GlueMatic 1011

EAN 4007841 084318
Article number 084318



Serie 1

Ø 11 mm

Klebesticks

13 g/min

Fördermenge



200°C



Aufheizzeit 8min

Function description

Our GM 1011 is the perfect solution for everyday use. With a flow rate of 13 g/min. and 11 mm glue sticks, it offers plenty of scope for creative bonding projects.

Technical specifications

Output	45 W	Suitable for	Sheetings, Glass, Wood, ceramic, Metal, Paper, Paper, lacquered, Card / cardboard boxes
Temperature	200 °C	Melt temperature	200 °C
Warm-up time	7 – 8 min	Cord length	2 m
Delivery rate	13 gr/min	Dimensions (L x W x H)	170 x 45 x 230 mm
Max. stick diameter	11 mm	PU1, net weight	0,303 kg
Idle mode	No	Manufacturer's Warranty	3 years
Nozzle can be changed	No	PU1, EAN	4007841084318
Stroke adjustment	No	Scope of delivery	incl. 2 glue sticks
Temperature, adjustable	No	Power plug	Typ C
Temperature accuracy +/-	10 °C	Average power consumption	40 W
Voltage range (min)	100 V		

Accessories

EAN 4007841 006754	Glue sticks Ø 11 mm Crystal
EAN 4007841 006761	Glue sticks, Ø 11 mm Ultra-Power
EAN 4007841 006815	Color sticks Ø 11 mm
EAN 4007841 064891	Glitter Sticks Ø 11 mm

<https://www.steinell.de>

Subject to technical modifications

10.2023 Page 1 from 1