

Hot-melt glue applicator

GlueMatic 3011

Case
EAN 4007841 085360
Article number 085360



Serie 3

Ø 11 mm


Klebesticks

16 g/min

Fördermenge



200 °C



austauschbare Düse

Function description

Tried-and-tested STEINEL technology! Our popular GM 3011 hot glue gun is suitable for large and small repair and craft projects. Simply glue, repair and conserve resources.

Technical specifications

Output	45 W
Temperature	200 °C
Warm-up time	7 min
Delivery rate	16 gr/min
Max. stick diameter	11 mm
Function, hanger	No
Soft grip	Yes
Idle mode	No
Nozzle can be changed	Yes
Stroke adjustment	No
Temperature, adjustable	No
Temperature accuracy +/-	10 °C

Voltage range (min)	100 V
Suitable for	Sheetings, Glass, Rubber, Wood, ceramic, Metal, Paper, Paper, lacquered, Card / cardboard boxes, Plexiglas®, PVC
Melt temperature	200 °C
Cord length	2 m
Dimensions (L x W x H)	256 x 53 x 180 mm
Version	Case
PU1, net weight	0,358 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841085360
Scope of delivery	incl. 3 glue sticks
Average power consumption	40 W

Accessories

EAN 4007841 006754

Glue sticks Ø 11 mm Crystal

EAN 4007841 044930

Glue sticks, Ø 11 mm Ultra-Power

<https://www.steinell.de>

Subject to technical modifications

10.2023 Page 1 from 2

Hot-melt glue applicator

GlueMatic 3011

Case
EAN 4007841 085360
Article number 085360



Accessories

EAN 4007841 006815

Color sticks Ø 11 mm

EAN 4007841 064891

Glitter Sticks Ø 11 mm
