

GlueMatic 7011

Folding box
 EAN 4007841 086947
 Article number 086947



Serie 7

ø 11 mm

Klebesticks

35 g/min

Fördermenge



40 - 230°C



stepless adjustable



Quick Start 2min

Function description

In continuous daily use, the GM 7011 with its powerful delivery rate, short heat-up time and temperature settings from 40-230°C is indispensable for processing a wide range of materials.

Technical specifications

Output	400 W
Temperature	40 – 230 °C
Warm-up time	2 min
Delivery rate	35 gr/min
Max. stick diameter	11 mm
Temperature display	LCD display
Function, hanger	No
Soft grip	Yes
Idle mode	Yes
Nozzle can be changed	Yes
Stroke adjustment	Yes
Temperature, adjustable	Yes
Temperature accuracy +/-	5 °C

Heating element	PTC heating element
Voltage range (min)	220 V
Suitable for	Glass, Rigid PVC, Wood, ceramic, Leather, Paper, Paper, lacquered, Card / cardboard boxes, Tarpaulins, Plexiglas®, PVC, Polystyrene, Textiles
Melt temperature	40 – 230 °C
Cord length	max.
Dimensions (L x W x H)	230 x 70 x 290 mm
Version	Folding box
PU1, net weight	1,015 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841086947
Power plug	Typ F
Average power consumption	110 W

Accessories

EAN 4007841 050092

General-purpose glue sticks Ø 11 mm

Hot-melt glue applicator - Professional Line

GlueMatic 7011

Folding box
EAN 4007841 086947
Article number 086947



Accessories

EAN 4007841 052430	Fast glue sticks Ø 11 mm
EAN 4007841 052423	Flex glue sticks Ø 11 mm
EAN 4007841 052409	Low Melt glue sticks Ø 11 mm
EAN 4007841 052416	Acrylate glue sticks Ø 11 mm