

GlueMatic 7011

Case set
 EAN 4007841 086954
 Article number 086954



series 7

ø 11 mm

Glue sticks

35 g/min

Delivery rate



40 - 230°C



stepless adjustable



Quick Start 2min

Function description

In continuous daily use, the GM 7011 with its powerful delivery rate, short heat-up time and temperature settings from 40-230°C is indispensable for processing a wide range of materials.

Technical specifications

Output	400 W	Melt temperature	40 – 230 °C
Temperature	40 – 230 °C	Cord length	max.
Warm-up time	1,5 – 2 min	Dimensions (L x W x H)	230 x 70 x 290 mm
Delivery rate	35 gr/min	Version	Case set
Temperature display	LCD display	PU1, net weight	1,015 kg
Nozzle can be changed	Yes	Manufacturer's Warranty	1 year
Temperature accuracy +/-	5 °C	PU1, EAN	4007841086954
Heating element	PTC heating element	Scope of delivery	incl. 3 universal glue sticks, long nozzle
Voltage range (min)	220 V	Power plug	Typ F
Suitable for	Sheetings, Glass, Rubber, Wood, ceramic, Leather, Paper, Card / cardboard boxes, Plexiglas®, Polystyrene, Textiles		

Accessories

EAN 4007841 052928	Long nozzle, Ø 1.5 mm
EAN 4007841 052935	Long nozzle
EAN 4007841 050092	General-purpose glue sticks Ø 11 mm

Hot-melt glue applicator - Professional Line

GlueMatic 7011

Case set
EAN 4007841 086954
Article number 086954



Accessories

EAN 4007841 052430	Fast glue sticks Ø 11 mm
EAN 4007841 052423	Flex glue sticks Ø 11 mm
EAN 4007841 052409	Low Melt glue sticks Ø 11 mm
EAN 4007841 052416	Acrylate glue sticks Ø 11 mm
EAN 4007841 087388	Glue sticks Ø 11 mm PUR set
EAN 4007841 052737	Long nozzle