

3 Outlet Dual USB Surge Protector



Description

3-Outlet Surge Protector with Dual USB Ports and Built-in Phone Holders All-in-one solution to keep your smartphones charging without sacrificing space or power outlets. This 3-outlet surge tap is rated at 1200 joules and features sliding smartphone-holding trays that retract when not in use. Compact and versatile, this 3-outlet surge tap eliminates cable clutter and keeps your smartphones, or tablets charged and ready for use.

Specifications

Housing Outlets	: Total Quantity Standard: 3
Housing Material	: PVC/ABS
Housing Outlets Configuration	: NEMA 5-15R
Electrical Ratings	: 15 Amps, 125 Volts, 1875 Watts, 60Hz
Unit Measurements (L×W×D)	: 125mm × 110mm × 35mm
Approval	: UL

Requirements		Specifications & Details
Male Plug	Male Blades	One Hot and One Neutral Male Blades for NEMA 5-15P
	Male Ground	One Male Ground Pin for NEMA 5-15P
	Male Plug:	Straight Plug, molded, 15A/125V, NEMA 5-15P
Protection	Joule Rating	1050 Joules
	Quantity	3 pcs
	Joule Rating per MOV	350 Joules
	Voltage Protection Rating (VPR)	500V
	EMI/RFI Filters	Attenuation: 0dB to 40dB
		Frequency: 150kHz to 30MHz
USB Charger	Max. Spike Voltage	6000V
	Number of Ports	2
	5 Volts (DC), 2.4 Amps (DC)	
USB Charger	Amp Rating per Port: 1.2A (Port 1), 1.2A (Port 2)	

Part Number Table

Description	Part Number
3 Outlet Dual USB Surge Protector	28-21305