


ANSI Type J PVC Insulated Mylar Screened Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Good general purpose insulation for 'light' environments.				
	Waterproof and very flexible.				
Cable Length	25, 50, 100 & 200m				
Cable Type	Twisted cores & screened construction for reduced				
	electrical noise				
Core / Strands	7/0.2mm				
Conductor Cross Section 7/0.2	0.219				
(mm2)					
Outer Colour	Black				
+ Colour	White				
- Colour	Red				
Drain Wire	Yes				
Insulation Material	PVC Insulated				
Loop Resistance 7/0.2	4.5				
(Ohms per combined metre)					
Max. Temperature	+105°C				
Min. Temperature	-10°C				
+ Conductor	Iron				
- Conductor	Constantan				
Screen	Mylar Screened				
Standards Met	Colour code (cores & jacket) to ANSI MC96.1				
Thermocouple Type	J				
Tolerance	Class 2				

Ordering Information

Туре	Colour Code	Cable Style	Strand Size	Length	Manufacturers Code	Farnell Order Code
J	ANSI	PVC MYLAR	7/0.2mm	25m (82ft)	WJ-241-ANSI	2443682
J	ANSI	PVC MYLAR	7/0.2mm	50m (164.1ft)	WJ-241-ANSI	4073508
J	ANSI	PVC MYLAR	7/0.2mm	100m (328.1ft)	WJ-241-ANSI	2443683
J	ANSI	PVC MYLAR	7/0.2mm	200m (656.2ft)	WJ-241-ANSI	2443684

TC Cable - 12 Nov-23



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers



ANSI PTFE Insulated Twin Twisted Farnell 2443696 Newark 73AC8304

ANSI PFA Insulated Twin Twisted Farnell 2443711 Newark 73AC8297

Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.


Best Sellers



Washer Thermocouple Farnell 8597952 Newark 38K1555

Bayonet Thermocouple Farnell 2785115 Newark 37AC0993

> Magnet Thermocouple Farnell 2081298 Newark 88T2877



Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers



ANSI Type K Exposed Junction Farnell 2443720 Newark 84X0232

IEC Type T Exposed Junction Farnell 7076186 Newark 68C2613

IEC Type K Exposed Junction Farnell 4100748



Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.

Best Sellers



IEC Thermocouple PCB Socket Farnell 2347056 Newark 06X5514



IEC Thermocouple Plug Farnell 7086362

Newark 67C1559



ANSI Thermocouple Socket

> Farnell 2347121 Newark 06X4819



RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers



PT1000 Thin Film Detector Farnell 8598550 Newark 38K0883

Newark 15J1022

PT100 Wire **Wound Detector**

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector Farnell 8598525

Newark 38K0885

Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.

Best Sellers



ANSI Thermocouple Farnell 2420317 Newark 53X3217

IEC Thermocouple with Mini Plug Farnell 4248338

Newark 19J1166

IEC Melt Bolt Thermocouple Farnell 2816490 Newark 44AC8638



Best Sellers

Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974



Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor

Farnell 2816462 Newark 44AC8648

L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers







L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.

TC Cable - 12

Nov-23