


# IEC Type J PFA Insulated Twin Twisted Pair Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

### Datasheet



#### Specifications

| General Description                   | Resistant to oils, acids other adverse agents and<br>fluids. Good mechanical strength and flexibility.<br>PTFE better for steam/elevated pressure<br>environments. |  |  |
|---------------------------------------|--|--|--|
| Cable Length                          | 10m, 25m, 50m, 100m  |  |  |
| Cable Type                            | Single pair of PFA insulated conductors twisted together   |  |  |
| Core / Strands                        | 1/0.2mm / 1/0.3mm, 1/0.508mm   |  |  |
| Conductor Cross Section 1/0.2 (mm2)   | 0.032  |  |  |
| Conductor Cross Section 1/0.315 (mm2) | 0.078  |  |  |
| Conductor Cross Section 1/0.508 (mm2) | 0.203  |  |  |
| + Colour                              | Black  |  |  |
| - Colour                              | White  |  |  |
| Drain Wire                            | No   |  |  |
| Insulation Material                   | PFA Teflon®  |  |  |
| Loop Resistance 1/0.2                 | 19.3   |  |  |
| (Ohms per combined metre)             |  |  |  |
| Loop Resistance 1/0.315               | 7.8  |  |  |
| (Ohms per combined metre)             |  |  |  |
| Loop Resistance 1/0.508               | 3.0  |  |  |
| (Ohms per combined metre)             |  |  |  |
| Max. Temperature                      | +260°C   |  |  |
| Min. Temperature                      | -75°C  |  |  |
| + Conductor                           | Iron   |  |  |
| - Conductor                           | Constantan   |  |  |
| Screen                                | No   |  |  |
| Standards Met                         | Colour code (cores & jacket) to IEC-584-3  |  |  |
| Thermocouple Type                     | J  |  |  |
| Tolerance                             | Class 1  |  |  |
|                                       |  |  |  |

## Datasheet

### Ordering Information

ABFAC

TEMPERATURE & PROCESS TECHNOLOGY

| Туре | Colour<br>Code | Cable Style      | Strand Size | Length         | Manufacturers<br>Code | Farnell<br>Order |
|------|----------------|------------------|-------------|----------------|-----------------------|------------------|
|      |                |                  |             |                |                       | Code             |
| J    | IEC            | PFA TWIN TWISTED | 1/0.2mm     | 10m (32.8ft)   | WJ-251-D              | 3582299          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.2mm     | 25m (82ft)     | WJ-251-D              | 3582297          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.2mm     | 50m (164.1ft)  | WJ-251-D              | 3582298          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.2mm     | 100m (328.1ft) | WJ-251-D              | 3582300          |
|      |                |                  |             |                |                       |                  |
| J    | IEC            | PFA TWIN TWISTED | 1/0.3mm     | 10m (32.8ft)   | WJ-252-D              | 3582303          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.3mm     | 25m (82ft)     | WJ-252-D              | 3582301          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.3mm     | 50m (164.1ft)  | WJ-252-D              | 3582302          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.3mm     | 100m (328.1ft) | WJ-252-D              | 3582304          |
|      |                |                  |             |                |                       |                  |
| J    | IEC            | PFA TWIN TWISTED | 1/0.508mm   | 10m (32.8ft)   | WJ-253-D              | 3582307          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.508mm   | 25m (82ft)     | WJ-253-D              | 3582306          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.508mm   | 50m (164.1ft)  | WJ-253-D              | 3582305          |
| J    | IEC            | PFA TWIN TWISTED | 1/0.508mm   | 100m (328.1ft) | WJ-253-D              | 3582308          |

