
THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, MITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

© 2003, Projects Unlimited Inc.

SPECIFICATIONS

	REVISIONS		
LTR	DESCRIPTION	DATE	APPROVED
ı	RELEASED FROM ENGINEERING	7/19/05	
Ā	REVISED TERMINAL MATERIAL	01/20/06	B.R.

PARAMETERS	VALUES	UNITS
RATED VOLTAGE (SQUARE WAVE)	3.6	Vp-p
OPERATING VOLTAGE RANGE	3 ~ 4.6	Vp-p
RATED CURRENT (MAX)	100	mA
COIL RESISTANCE	18±5	ОНМ
MINIMUM SPL @ 10 CM	93	dBA
RESONANT FREQUENCY	2,830±500	Hz
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-40 ~ +85	•c
HOUSING MATERIAL	PA46	=
TERMINAL MATERIAL	Au PLATED COPPER	-
WEIGHT	0.9	grams



NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2002/95/EC COMPLIANT

APPROVALS DATE DRAWN R.C. 7/05 APPROVED E. P. 7/05 SMT-1028-S-R.DWG DO NOT SCALE DRAWING

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.2 AND
ANGLES ARE ±3'.

projects ® unlimited SURFACE MOUNT TRANSDUCER DRAWING NO. SIZE SMT-1028-S-R

Dayton , Ohio

SHEET 1 OF SCALE: N.T.S.