



# Nylon Metric Cable Glands

## Range: Cable Glands/Grommets

Part Number: K341-1025-00



### DESCRIPTION

Kwik Fix cable gland PA7035 M25

### CABLE GLANDS/GROMMETS FEATURES

- IP68
- Temp range -20°C to +100°C
- Quick and easy installation without special tools
- Assemble from one side only - no separate lock nut, saves time so saves money
- Wall thickness 1-4mm

*Subject to technical modification without notice.*

*Typographical and other errors do not justify claim for damages.*

## SPECIFICATION

<b>Product Type</b>	Standard
<b>Sealing Ring Material</b>	Polychloroprene-Nitrile rubber CR/NBR
<b>Body Material</b>	Polyamide
<b>Mounting Nut Material</b>	Polyamide PA6 GF30
<b>Moulded Sealing Ring Material</b>	Nitrile-Polytetrafluorethylene rubber NBR/PTFE
<b>Min Temperature Rating °C</b>	-20
<b>Max Temperature Rating °C</b>	100
<b>IP Rating</b>	68
<b>Colour</b>	Light Grey - RAL 7035
<b>Hole Diameter (mm)</b>	25.1
<b>Thread Size</b>	M25
<b>Clamping Range Min (mm)</b>	11
<b>Clamping Range Max (mm)</b>	17
<b>External Connecting Thread Type</b>	Metric
<b>Width Across Flat 1 (mm)</b>	32
<b>Width Across Flat 2 (mm)</b>	29
<b>Height (mm)</b>	48
<b>Additional Material Detail</b>	Body - Polyamide PA6 V-2