



Venting Elements/Breather Plugs

Range: Cable Glands/Grommets

Part Number: JDAE12ES4305



DESCRIPTION

M12 Stainless Steel Venting element thread length 6

CABLE GLANDS/GROMMETS FEATURES

- Typical air flow 90 - 130 ml/min/cm²; at $\Delta p = 0,01$ bar
- Water entry pressure > 1 bar
- Temperature range -40°C/+100°C
- Protection grade IP66 / IP67 / IP69K

Subject to technical modification without notice.

Typographical and other errors do not justify claim for damages.

SPECIFICATION

Product Type	Standard
Body Material	Stainless steel 1.4305
Min Temperature Rating °C	-40
Max Temperature Rating °C	100
IP Rating	IP66/IP67/IP69K
External Connecting Thread Type	Metric
Thread Length (mm)	6
Membrane	Polyether sulphone PES
Typical Air Flow	90 - 130 ml/min/cm2, 0,01 bar
Water Entry Pressure	> 1 bar
Width Across Flat 1 (mm)	17
Height (mm)	13
Connecting Thread Size	M12x1.5
Test Standard	Sleeve - Stainless steel 1.4305, O-Ring - Nitrile rubber