


IEC PTFE Single Shot Exposed Junction Thermocouple with Miniature Plug - Type K, T



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

•	Unique single shot cable construction Resistant to chemicals, oils and fluids. Suitable for aerospace applications and is wildly used in autoclaves.			
Sensor Type	Exposed Junction			
Thermocouple Type	K&T			
Cable Length	1, 2, 5 & 10m			
Cable Type	PTFE			
Core / Strands	1/0.376mm			
Termination Type	Terminated with a miniature flat pin plug (Plug max temp 220°C)			
Max. Temperature	+250°C			
Standards Met	IEC-584-3			
Connector Type	Plug			
Connector Size	Miniature			

Ordering Information

Туре	Style	Material	Cable Size	Length	Termination	Manufacturers Code	Farnell Order Number
K	SINGLE SHOT	PTFE	1/0.376mm	1m (3.3ft)	Miniature Plug	Z2-K-1M-C25-1/0.376-MP	3584254
K	SINGLE SHOT	PTFE	1/0.376mm	2m (6.56ft)	Miniature Plug	Z2-K-2M-C25-1/0.376-MP	3584255
K	SINGLE SHOT	PTFE	1/0.376mm	3m (9.84ft)	Miniature Plug	Z2-K-3M-C25-1/0.376-MP	4073372
K	SINGLE SHOT	PTFE	1/0.376mm	5m (16.4 ft)	Miniature Plug	Z2-K-5M-C25-1/0.376-MP	3584256
K	SINGLE SHOT	PTFE	1/0.376mm	10m (32.8ft)	Miniature Plug	Z2-K-10M-C25-1/0.376-MP	3584257
Т	SINGLE SHOT	PTFE	1/0.376mm	1m (3.3ft)	Miniature Plug	Z2-T-1M-C25-1/0.376-MP	3584258
Т	SINGLE SHOT	PTFE	1/0.376mm	2m (6.56ft)	Miniature Plug	Z2-T-2M-C25-1/0.376-MP	3584259
T	SINGLE SHOT	PTFE	1/0.376mm	3m (9.84ft)	Miniature Plug	Z2-T-3M-C25-1/0.376-MP	4073371
Т	SINGLE SHOT	PTFE	1/0.376mm	5m (16.4 ft)	Miniature Plug	Z2-T-5M-C25-1/0.376-MP	2785104
T	SINGLE SHOT	PTFE	1/0.376mm	10m (32.8ft)	Miniature Plug	Z2-T-10M-C25-1/0.376-MP	3584260

EJ - 14 Nov-23



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers 📥



ANSI PTFE
Insulated Twin
Twisted
Farnell 2443696
Newark 73AC8304

ANSI PFA Insulated
Twin Twisted
Farnell 2443711
Newark 73AC8297

Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

Best Sellers



Washer Thermocouple Farnell 8597952 Newark 38K1555

Bayonet Thermocouple Farnell 2785115 Newark 37AC0993

Magnet
Thermocouple
Farnell 2081298
Newark 88T2877

Exposed Junction

Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

Thermocouples

 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers



JEC Type T Exposed Junction Farnell 7076186 Newark 68C2613

IEC Type K Exposed Junction Farnell 4100748 Newark 15J1022



Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



PCB Socket Farnell 2347056 Newark 06X5514



IEC Thermocouple Plug

Farnell 7086362 Newark 67C1559





RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers



Farnell 8598550 Newark 38K0883

PT100 Wire Wound Detector

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector Farnell 8598525

Newark 38K0885



Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





ANSI Thermocouple Farnell 2420317 Newark 53X3217

IEC Thermocouple with Mini Plug Farnell 4248338

Newark 19J1166

IEC Melt Bolt

IEC Melt Bolt Thermocouple Farnell 2816490 Newark 44AC8638



Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.

Best Sellers



Sensor Probe Farnell 8598096 Newark 38K0974

Pt100 Sensor in
Stainless Steel Tube
with Teflon Lead
Farnell 2420300
Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor Farnell 2816462

Newark 44AC8648

L60 Fine Wire

Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers





L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

EJ - 14 Nov-23