PowerVerter DDi 48-12 072

voltage converter

from Alfatronix

The unit has the following key benefits:

- Quick and easy to connect
- Power rating to 72W continuous (96W intermittent)
- Cool running switch mode design with efficiency typically 85%
- Internal protection against over current, transients and overheating.
- No quibble warranty



Characteristics	
Input Voltage Range	48Vdc nominal (33-55V)
Output Voltage	13.6.2Vdc +/- 10%
Continuous Current Rating	13.6V output rated at 6A continuous
Intermittent Current Rating	13.6V output 10A taken for a maximum of 2 minutes followed by 8 minutes rest.
Transient Voltage Protection	Meets ISO7637-2 International Standard for 24Vdc Commercial Vehicles.
Electro Static Voltage Protection	Meets ISO10605, ISO14892, >8kV contact, 15kV discharge.
Output Noise	<50mV pk-pk at continuous load. Meets CISPR25 and VDE0879-3
Off load current (quiescent current)	<30mA. If connected to the battery, but not powering any equipment.
Power Conversion Efficiency	Typically 85%
Isolation	>400Vrms between input, output and case
Operating Temperature	-25°C to +30°C. +30°C to +80°C de-rate linearly to 0A
Storage Temperature	-25°C to +80°C
Operating Humidity	95% non-condensing.
Case Work	Anodized Aluminum, Dust, water and impact resistance IP533
Connections	4 off 6.3mm push on crimp connectors
Weight and Dimensions	Weight: 405g Dimensions 127 (L) x 87 (W) x 50 (H) mm
Mounting Method	"Click 'n' Fit" mounting clip, fitted separately using three hole fixing
Safe Area Protection: Over Current Over Heat Transients Catastrophic failure	Limited by current sensing circuit Limited by temperature sensing circuit Protected by filters and rugged component selection Protected by input and output fuses
Approvals	89/336/EEC The General EMC Directive 95/54/EC The Automotive EMC Directive (pending) 93/68/EEC The CE Marking Directive
Tested to	ISO7637, ISO10605, ISO11451, ISO11452, CISPR 25, VDE0879-3, EN60945
Markings	CE marked and e marked No e11 020324



AlfaTronix Limited 29 Newtown Business Park, Poole, Dorset BH12 3LL Great Britain Telephone: +44 (0) 1202 715517. Fax: +44 (0) 1202 715122. E-mail: sales@alfatronix.ltd.uk. Website: http://www.alfatronix.ltd.uk. An ISO9001 Registered Company