



description:

A high quality, miniature, omni-directional, electret condenser microphone with integral FET, incorporating internal capacitors for GSM and DECT RFI protection..

technical information:

Technical Data	-
Model	MD6022ASC-0
Directivity	Omni-directional
Sensitivity	-42dBV/Pa 3dB
Impedance	2.2kOhm
Current	0.5mA
S/N Ratio	52dB
Frequency Range	100Hz-10kHz
Terminals	Solder
Capacitors	33pF and 10pF
Operating Temperature	-20C to +50C
Operating Voltage	2V
Max. Input Sound Level	120dB SPL
Dimensions (Dia.xH)	6x2.2mm