


AMP WIRE RANGE	Listed FILE E13200	LR7189 Certified
	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

METRIC

DIMENSIONS LISTED IN mm (INCHES)

NOTE:

1. WIRE INSULATION DIA 2.03(.080) TO 3.18(.125)
2. MARKING 22-18 FOR MILITARY COMMERCIAL RANGE 22-16



100	LOOSE PIECE, BOX SPL	8-320559-5
5	LOOSE PIECE, BLS	8-320559-4
50	LOOSE PIECE, BOX	8-320559-2
2500	ON TAPE	2-320559-4
50	LOOSE PIECE	320559
QTY	PACKAGE TYPE	PART NO
AMP AMP Incorporated Morrisburg, PA 17105-3608		
NAME SPLICER, BUTT, P.I.D.G., WIRE SIZE, 22-16 AWG		
SIZE	QTY	SCALE
B	00779	C-320559
SCALE	NTS	1 OF 1

DO NOT SCALE PRINT. DIMENSIONS SPECIFIED UNLESS OTHERWISE INDICATED. ALL DIMENSIONS UNLESS OTHERWISE SPECIFIED ARE IN MILLIMETERS. FINISH PER MIL-T-10727	MAY RECOMMENDED OPERATING TEMPERATURE: 105°C	VOLTAGE RATING: 300 V MAX 1000V MAX (PITURE OR BLENDED)	CIRCULAR MIL AREA: 0.26-1.85 mm ² (509-3,260)
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS 1-800-522-6752	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR MILITARY USE. IT IS THE PROPERTY OF AMP AND IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS WITHOUT THE WRITTEN PERMISSION OF AMP.
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS FOR APPLICATION TOOLING INFORMATION FOR ORDER ENTRY	1-800-522-6752 1-800-722-1111 1-800-526-5142	AMP10744 15106144	AMP10744 15106144 (111)201201113>AMP10744/1113