

Part Number: 39000038

Product Description: Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated

Brass, 18-24, 22+22 AWG, Reel

Series Number: 5556

Status: Active

Product Category: Crimp Terminals

Engineering Number: 5556T

Packaging Alternative: 0039000039 (Bag)



Documents & Resources

Drawings

Drawing 039000038_sd.pdf

Packaging Design Drawing 55560001-PK-000.pdf Packaging Design Drawing SPK-5556-001-001.pdf Packaging Design Drawing SPK-5556-001-002.pdf Packaging Design Drawing SPK-5556-001-003.pdf

Specifications

Application Specification 55560001-AS-000.pdf
Product Specification 55560002-PS-CH-000.pdf
Product Specification 55560002-PS-ES-000.pdf
Product Specification 55560002-PS-SK-000.pdf
Product Specification 55560008-TS-000.pdf
Product Specification PS-5556-001-001.pdf
Product Specification PS-5556-002-001.pdf
Test Summary 55560000-TS-000.pdf
Test Summary 55560010-TS-000.pdf
Test Summary TS-5556-002-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	©
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5556
Description	Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 18-24, 22+22 AWG, Reel
Application	Power, Wire-to-Board, Wire-to-Wire
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit
UPC	800753585010

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.182/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size (AWG)	18, 20, 22, 22+22, 24
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Receptacle Housings	<u>5557</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>44516</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>42474</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>43760</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>0011030044</u>
FineAdjust Applicator for Mini-Fit Double Crimp Applications Using Two 22 AWG Wires	<u>2037026300</u>
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 18-24 AWG	<u>0638190901</u>
FineAdjust Applicator for 18-20 AWG and 18-24 AWG Wires with Insulation Diameter 1.90-2.30mm	<u>0639015600</u>

FineAdjust Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	0639023900
FineAdjust Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	0639024800
FineAdjust Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	0639024900
FineAdjust Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG	0639047800
FineAdjust Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG	0639048000
T2 Terminator for Insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639115600</u>
T2 Terminator for insulation OD 1.40-1.70mm - 18-24 AWG	0639123900
T2 Terminator for insulation OD 2.50-2.95mm optimized for 18 AWG only	<u>0639124800</u>
T2 Terminator for insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639124900</u>
T2 Terminator for Mini-Fit Crimp Terminals, 18-24 AWG with Large Insulation ODs	<u>0639147800</u>
T2 Terminator for Mini-Fit Crimp Terminals, 18-24 AWG with Smaller Insulation ODs	<u>0639148000</u>

Application Tooling

Japan

Description	Part Number
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 18-24 AWG, UL1007 Wires	<u>0570223700</u>
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 18-24 AWG, UL1015 Wires	<u>0570223710</u>
Hand Extraction Tool	<u>0570316000</u>