

# Product data sheet

Specifications

SQUARE D

Green Premium™



Safety switch, heavy duty, fusible, 30A, 600VAC/VDC, 3 poles, 20hp, NEMA 12K, crouse hinds arktite

H361AWC

Product availability : Stock - Normally stocked in distribution facility

## Main

Product	Receptacle Switch
For Use With	Plug APJ3485 Crouse-Hinds Arktite
Disconnect Type	Fusible disconnect switch
Phase	3 phase
Number of Poles	3
Current rating	30 A
Voltage Rating	600 V AC 250 V DC
Enclosure Rating NEMA 3R	NEMA 12K
Maximum Horse Power Rating	5 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 600 V AC 50-60 Hz for 3 phase motors 5 hp at 250 V DC

## Complementary

Short-circuit Current Rating	10 kA H or K 200 kA R or J
Fuse Type	H or K R or J
Mounting Type	Surface
Electrical Connection	Receptacle
Wire Configuration	4-wire
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening torque	45 lbf.in (5.08 N.m) (AWG 6) 40 lbf.in (4.52 N.m) (AWG 8) 35 lbf.in (3.95 N.m) (AWG 14...AWG 10)
Depth	7 in (177.80 mm)
Width	10.5 in (266.70 mm)
Height	16.5 in (419.10 mm)
Net Weight	28.66 lb(US) (13 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00118-H&HU SW,W/C-HINDS RECPT-WC
Discount Schedule	DE1
GTIN	785901076971
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.40 in (18.796 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	25.90 in (65.786 cm)
Package 1 Weight	23.00 lb(US) (10.433 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)