



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

- 1. BRASS PER QQ-B-626
- 2. BRASS PER QQ-B-613
- 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
- 4. PHOSPHOR BRONZE PER QQ-B-750
- 5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE

1. MAX. PANEL THICKNESS=5.5mm

						DIMENSIONS ARE IN MILLIMETERS				PART NO. B7771B3-ND3G-50		Amphenol	
						UNLESS OTHERWISE SPECIFIED TOLERANCES				APPROVED	DATE		
7	HEX NUT	NOTE 1	NOTE 3	1	HN16-1/2-28X28	0.5-6 = ±0.2					10-11-01'	BNC FEMALE TO FEMALE BULKHEAD ISOLATED ADAPTOR	
6	LOCK WASHER	NOTE 2	NOTE 3	1	LW-16/13X05	6-30 = ±0.4				CHECKED	DATE		
5	LOCK RING	NOTE 2	NOTE 3	1	LR-79/62X08	30-120 = ±0.6					10-11-01'	DRAWING NO.	
4	CONTACT PIN	NOTE 4	NOTE 5	1	B7900-4	120-315 = ±1				DRAWN	DATE	KJ-B7771B3-ND3G-50	
3	INSULATOR	DELTRIN	NATURAL	2	B7996ZZ-3-50	315-1000 = ±1.6					10-11-01'	ITEM NO.	
2	INSULATOR	DELTRIN	WHITE	1	B7771B3-1P	1000-2000 = ±2.4							
1	BODY	NOTE 1	NOTE 3	1									
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	3/1	ISSUE	A	FILE NO.			

F
E
D
C
B
A

F
E
D
C
B
A

1 2 3 4 5 6 7 8