Brannan Product Data Sheet PDS0063.20.REV9

Electronic Max Min Indoor/Outdoor Thermometer

White moulded case with two displays for outdoor and indoor temperature. Each display has maximum and minimum recording facility and can be either Celsius or Fahrenheit. Complete with stand and external probe. Replacement probe also available.

Product Features:

- · Measures indoor and outdoor temperatures
- Freezing alert
- · 2m probe cable for remote reading
- · Desk stand and hanging hook
- Battery and full instructions included

Product Specifications:

Temperature Range: Indoor (internal reading): 0 to +50°C&F

Outdoor (external probe reading): -50 to +70°C&F

Divisions: 0.1°C/F

Accuracy: +/-2°C between -20 & 0°C

+/-1°C between 0 & +50°C +/-2°C between +50 & +70°C

Probe: Thermistor Probe IP67

Sampling Rate: 10 seconds

Battery: 1 x AAA (supplied)

CE & RoHS/WEEE: Compliant
Cable Length: 2500mm
LCD Dimensions: 35 x 52mm

Dimensions: Net: 98 x 74 x 17mm

Gross: 138* x 95 x 24mm

Weights: Net: 79g

Display box: 33.5g Gross: 112.5g



Description	Barcode	Product No
Digital Max MinThermometer	5 011405 124128	12/412/3
Replacement Probe	n/a	12/412/1





^{*} Box height has additional 32mm for Euroslot extension.