

# Product data sheet

✉ [sales@brannan.co.uk](mailto:sales@brannan.co.uk)

☎ +44 (0)1946 816600

🌐 [brannan.co.uk](http://brannan.co.uk)

## ELECTRONIC TEST THERMOMETER WITH PROBE

Electronic thermometer with robust stainless steel probe. Temperature hold and max min functions. Supplied with hanger, stand and magnetic fixtures.



### Functions:

- Wide measurement range
- Max/Min temperature memory
- Data hold function
- Large, clear LCD
- Hanger, stand and magnet fixture

### Product specifications:

**Measuring range:** -20°C to 200°C/-58°F to 392°F

**Accuracy:** ±1°C (19.9°C to 199°C)  
± 1°C (-50°C to 100°C) otherwise ± 2.5°C

**Resolution:** ±1°C (19.9°C to 199°C) otherwise 1°C

**Sampling rate:** 1 second

**Cable:** 1m

**Probe length:** 235mm

**Battery:** 1pc x AAA

**CE/ROHS/WEEE:** Compliant

**Hazard information (SDS):** See [brannan.co.uk](http://brannan.co.uk) for information

**Product weight:** Net: 96g (including batteries)

Gross: 137g (including 41g box)

**Product dimensions:** 97mm x 65mm x 20mm (main unit)

**Gross dimensions:** 220 x 112 x 31mm

Description	Barcode	Product No
Test thermometer	5 011405 386502	38/650/0
Replacement probe	-	38/650/1



View me on  
the website





Measurement for life.



# Product data sheet


 [sales@brannan.co.uk](mailto:sales@brannan.co.uk)


 [+44 \(0\)1946 816600](tel:+44(0)1946816600)

 [brannan.co.uk](http://brannan.co.uk)

# Product data sheet

 [sales@brannan.co.uk](mailto:sales@brannan.co.uk)

 [+44 \(0\)1946 816600](tel:+44(0)1946816600)

 [brannan.co.uk](http://brannan.co.uk)