

ITT *143-394 to 397* Sounders

✓ Piezo Ceramic Sounders

- Sound outputs from 70-105dbA
- Choice of continuous or pulsed tone
- Solid state oscillators
- Low power consumption
- No contact arcing

143-403

Output tones available are indicated within the part number R-continuous tone; DI-10Hz pulsed tone; D2-2Hz pulsed tone

Part Number	Dimensions mm	Voltage dc	Current mA	Output freq. kHz	Sound level dB	Weight g
U4B21R	17 D 23 dia.	12	6	3	>70	4.5
U420R	17 D 21 dia.	12	4	3	>75	5
U535R	40 H 40W 8 D	12	6	3.3	>75	12
U350R	60 H 60 W 10 D	12 or 24	8	2.7	>80	50
U150RD1 U150RD2	80 H 60 W 10 D	12 or 24	10	2.7	>85	40
U250RD1D2	33 Deep 60 dia 70 fixing centres	12 or 24	10	2.7	>85	70
U250RD1D2H U250RD2H U250D2H U250RHA U250D2HA	36 Deep 90 dia	24 12 12 12 12	10 10 10 18 18	2.7 2.7 2.7 2.7 2.7	>90 >90 >90 >105 >100	150