

# Product data sheet

Specifications



Earth braids section 6mm<sup>2</sup>, length 150mm, eyebolt 7mm. Packaging unit: 10.

NSYEB156D6

Product availability : Stock - Normally stocked in distribution facility

## Main

Range	Spacial
Anwendung	Multi-purpose
Product or Component Type	Earthing braid
Device composition	1 braid
Quantity per Set	Set of 10

## Complementary

Material	Tinned copper
Fixing mode	Nut and washer - on earth connection
Length	5.91 in (150 mm)
Width	0.47 in (12 mm)
Nominal cross section	0.01 in <sup>2</sup> (6 mm <sup>2</sup> )
Diameter	0.28 in (7 mm)

## Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480181337
Returnability	No
Country of origin	IT

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.20 in (0.5 cm)
Package 1 Width	4.72 in (12.0 cm)
Package 1 Length	8.66 in (22.0 cm)
Package 1 Weight	0.42 oz (12.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)