

Product data sheet

Specifications

SQUARE D



Timing Relay, Type A, pneumatic, enclosure, for 9050A , NEMA 1, sheet steel, painted grey

9991UE6

Main

| | |
|---------------------------|-----------|
| Product or Component Type | Enclosure |
|---------------------------|-----------|

Complementary

| | |
|---------------------|--|
| Depth | 5.53 in (140.46 mm) |
| Enclosure material | sheet steel |
| Height | 5.75 in (146.05 mm) |
| Product destination | Contactor class 8910 H pneumatic timers 9050A |
| Width | 4.91 in (124.71 mm) |

Environment

| | |
|---------------------------|--------|
| NEMA Degree of Protection | NEMA 1 |
|---------------------------|--------|

Ordering and shipping details

| | |
|-------------------|--------------------------------|
| Category | 21743-9991 MISC. (NOT P,S,UE1) |
| Discount Schedule | CP1 |
| GTIN | 785901493488 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.54 in (6.452 cm) |
| Package 1 Width | 1.00 in (2.54 cm) |
| Package 1 Length | 6.45 in (16.387 cm) |
| Package 1 Weight | 2.70 lb(US) (1.225 kg) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the |
|---------------------------|---|

| | |
|----------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)