

# Product data sheet

Specifications

SQUARE D

Green Premium™



Enclosure, PowerPacT P, circuit breaker, 250 to 1200A, NEMA 12/3R, no knockouts, 2 to 3 pole

P1200AWK

Product availability : Stock - Normally stocked in distribution facility

## Main

Circuit Breaker Type	PJL PLL PKL MGL PGL MJL
----------------------	--

Breaker Compatibility	Circuit breaker M 3P Circuit breaker P 2P
-----------------------	--

## Complementary

Rated Current	250... 1200 A
Poles Description	3P 2P
Enclosure Material	Steel
Height	53.00 in (1346.2 mm)
Width	20.75 in (527.05 mm)
Depth	9.50 in (241.3 mm)
Product Weight	104.70 lb(US) (47.49 kg)

## Environment

Product Certifications	UL CSA
------------------------	-----------

## Environmental

NEMA Degree of Protection	NEMA 12K
---------------------------	----------

## Ordering and shipping details

Category	00031-IND CB ENC N 4,4X,5,12,12K
Discount Schedule	DE1
GTIN	785901433217
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.50 in (34.29 cm)
Package 1 Width	22.50 in (57.15 cm)
Package 1 Length	56.70 in (144.018 cm)
Package 1 Weight	104.70 lb(US) (47.49 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)