



Part Number : [2237940501](#)

Product Description : Micro-Fit+ Plug Housing, Single Row, 5 Circuits, UL 94V-0, Free Hanging, Glow-Wire Capable, Black

Series Number : 223794

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 2237940501_sd.pdf](#)

[Packaging Design Drawing 2237940000-PK-000.pdf](#)

3D Models and Design Files

[3D Model 2237940501_stp.zip](#)

Specifications

[Product Specification 2159530000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	223794
Description	Micro-Fit+ Plug Housing, Single Row, 5 Circuits, UL 94V-0, Free Hanging, Glow-Wire Capable, Black
Application	Power, Wire-to-Wire
Product Family	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	196823498329

Physical

Circuits (maximum)	5
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.940/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit+ Single Row Receptacle Housings	<u>215759</u>

Use with Part(s)

Description	Part Number
Micro-Fit+ Terminal Position Assurance (TPA) Retainers	<u>206462</u>
Micro-Fit+ Male Crimp Terminals	<u>215953</u>