

NEW SANDFLEX® BI-METAL, 3906

The virtually unbreakable and shatterproof Bi-metal blade with precision ground teeth for all kinds of metal sawing. With a blade back of strong, flexible spring steel and a tooth line in high-alloyed super high speed steel, this blade is guaranteed to keep its sharpness for a long time. The new SANDFLEX® blade combines extreme cutting performance and wear resistance with a high degree of flexibility and is vastly superior to all-hard high speed blades or conventional, flexible blades.

Packaging of -100: 10 bundles of 10 blades in black, plastic box with transparent cover.



(C) (FA)	Lx W x 7	\(\sum_{\text{person}}\) \(\Delta_g^{\dagger}\)
----------	----------	---

3906-300-18-100	8233532	100	300x13x0.65	18	17
3906-300-24-100	8233549	100	300x13x0.65	24	17
3906-300-32-100	8233556	100	300x13x0.65	32	17