



Oblique cutters, 4239 ergo®

Oblique cutter with 45° cutting angle, for fine mechanical, telecommunication and electronics industry. Equipped with return spring. Numerically controlled machine grinding guarantees edge angle accuracy.

ISO: 5748, DIN: 5748

Material: High performance tool steel

Finish: Black oxidised.

Cutting capacity: Copper wire



				A mm	B mm	C mm	D	E	F	G		
4239		0100088	3	129	19	9	7	3.0	1.5	5.5	0.3-1.0	Flush 60