



**Part Number :** [2240861064](#)  
**Product Description :** Mini-Fit Max Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Tin(Sn) Plating, 6 Circuits, 600.00mm Length, 2.5mm<sup>2</sup> Wire, Black  
**Series Number :** 224086  
**Status :** Active  
**Product Category :** Power and Signal Cable Assemblies



Documents & Resources

**Drawings**  
[Drawing 2240861064\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

|                        |                                                                                                                                                 |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                                                          |
| Category               | Power and Signal Cable Assemblies                                                                                                               |
| Series                 | 224086                                                                                                                                          |
| Description            | Mini-Fit Max Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Tin(Sn) Plating, 6 Circuits, 600.00mm Length, 2.5mm <sup>2</sup> Wire, Black |
| Application            | Power, Wire-to-Board, Wire-to-Wire                                                                                                              |
| Assembly Configuration | Single Ended Connector                                                                                                                          |
| Connector to Connector | Mini-Fit Max-to-Pigtail                                                                                                                         |
| Product Family         | Mini-Fit Family Power Connectors                                                                                                                |
| Product Name           | Mini-Fit Max                                                                                                                                    |
| Type                   | Discrete Wire Assembly                                                                                                                          |
| UPC                    | 196823397318                                                                                                                                    |

### Electrical

|                               |               |
|-------------------------------|---------------|
| Current - Maximum per Contact | 20A           |
| Voltage - Maximum             | 600V AC (RMS) |

### Physical

|                                |                          |
|--------------------------------|--------------------------|
| Cable Length                   | 600.00mm                 |
| Circuits (Loaded)              | 6                        |
| Circuits (maximum)             | 6                        |
| Color - Resin                  | Black                    |
| Gender                         | Female-Pigtail           |
| Lock to Mating Part            | Yes                      |
| Material - Metal               | High Conductivity Copper |
| Material - Plating Mating      | Tin                      |
| Material - Plating Termination | Tin                      |
| Material - Resin               | Nylon                    |
| Net Weight                     | 87.269/g                 |
| Number of Rows                 | 2                        |
| Overmolded                     | No                       |

|                             |                      |
|-----------------------------|----------------------|
| Packaging Type              | Bag                  |
| Pitch - Mating Interface    | 4.20mm               |
| Plating min - Mating        | 1.020µm              |
| Plating min - Termination   | 2.540µm              |
| Single Ended                | Yes                  |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type             | UL 11028             |
| Wire Insulation Diameter    | 2.65mm               |
| Wire Size (AWG)             | 14                   |

---

## Mates With / Use With

### Mates with Part(s)

| Description                            | Part Number   |
|----------------------------------------|---------------|
| Mini-Fit Max Vertical Dual Row Headers | <u>212520</u> |