

ROLINE S/FTP Patch Cord Cat.5e (Class D), grey, 1 m

| | |
|---------------------------|---------------|
| Product No. | 21.15.0301 |
| Manufacturer | ROLINE |
| Manufacturer No. | 21.15.0301 |
| EAN (single piece) | 7611990136896 |



Patch cable for networking connections between devices. Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends. Durable due to moulded kink protection. Flexible cable, suitable for narrow bending. High quality plugs with gold plated contacts. Contact settings 1:1, in accordance with the EIA/TIA 568 standard. Construction: 4-pair stranded copper wire. Complete braid shielding and aluminium clad polyester foil.

For a structured cabling system we recommend to use the following components: ROLINE Cat.5e S/FTP Cable, Solid Wire, AWG24: 21.15.0019 (100 m), 21.15.0020 (300 m); ROLINE Cat.5e Flush/Surface Mount Wall Jack, shielded: 25.16.8487 (white), 25.16.8486 (ivory)/25.16.8387 (white), 25.16.8386 (ivory); ROLINE Cat.5e 19" Patch Panel, 24 Ports, shielded: 26.11.0329 (light grey), 26.11.0328 (black); ROLINE Cat.5e S/FTP Patch Cord, grey, 5 m: 21.15.0305. Our in-house laboratory has tested this cable-plug combination, in a Channel of 100 meters, in compliance with Class D specifications.

Technical specifications

| | |
|---------------|--------------------|
| Manufacturer | ROLINE |
| Product group | Twisted Pair Cable |
| Product type | S/FTP Patchcord |
| Colour | grey |

| | |
|------------------------------------|-----------------|
| Length | 1 m |
| Shield type | SFTP |
| Transfer quality | Cat5e / Class D |
| Impedance | 100 Ohm |
| Quantity of wires | 8 |
| Conductor type | Wire |
| Crossed | No |
| Colour (Spout) | grey |
| Cable LSOH | No |
| Side 1 Connector Type | RJ-45 |
| Side 1 Connector Gender | Male |
| Side 2 Connector Type | RJ-45 |
| Side 2 Connector Gender | Male |
| Connector Type RJ45 | Standard |
| Weight | 41.6 g |
| Height of packaging (single piece) | 20 mm |
| Width of packaging (single piece) | 150 mm |
| Depth of packaging (single piece) | 120 mm |
| Package weight (single piece) | 0.042 kg |