

## **3/8" Drive 6 Point Standard Metric Socket 18mm**



GEARWRENCH 3/8" drive sockets are manufactured from alloy steel for maximum durability and strength. Our off corner loading design reduces fastener rounding and the chamfered opening help guide the socket on to fasteners. Our sockets feature a double line (SAE) and knurled (metric) ring help easily identify standard and metric sockets.

## FEATURES

- Off-corner loading design reduces fastener rounding
- Chamfered opening quickly guides fasteners into socket
- Hard stamped size markings

## SPECIFICATIONS

SKU: 80386

Dim. A: Drive End: 0.937 in

Dim. B: Wrench End: 0.937 in

Dim. D: Bolt Clearance: 0.354 in

Prop 65: WARNING: This product contains or produces a chemical known to the State of California to cause cancer and birth defects or other reproductive harm.

Dim. E: Wrench Depth: 0.492 in

ASME Specification: B107.5M

Dim. F: Length to Shoulder: 0.453 in

Knurled: Yes

Overall Length: 0.984

Size: 18mm

ANSI Specification: Meets or Exceeds

Product Type: Socket

Packaging: Carded

Weight (Catalog): 0.11

Warranty: Full Lifetime

Drive Tang Size: 3/8 in

Socket Size (mm): 18mm

Length Format: Standard

Finish: Full Polish Chrome

Magnetic: No

SAE/Metric/Torx: Metric

UPC: 099575803864

Drive Type: 6 Point

Material: Alloy Steel