

3/8" Drive 6 Point 5/8" Magnetic Swivel Spark Plug Socket 6"



GEARWRENCH swivel magnetic spark plug sockets are manufactured from durable alloy steel with a full polish chrome finish to resist rust and corrosion. The swivel design gives better access to hard to reach spark plugs and the magnetic insert grips on to spark plugs making removal & installation easier.

FEATURES

- Swivel design provides better access to hard to reach spark plugs
- Off-corner loading design reduces fastener rounding
- Magnetic insert holds plug for removal and installation

SPECIFICATIONS

SKU: 80546

Prop 65: WARNING: This product contains or produces a chemical known to the State of California to cause cancer and birth defects or other reproductive harm.

Dim. E: Wrench Depth: 1.81 in

Bolt Depth: 1.81 in

ASME Specification: B107.34

Dim. A: Drive End Hex Across Flats: 0.748 in

Knurled: No

Overall Length: 6.0

Size: 5/8 in

ANSI Specification: Meets or Exceeds

Product Type: Socket

Packaging: Carded

Weight (Catalog): 0.43

Warranty: Full Lifetime

Socket Size (SAE): 5/8 in

Drive Tang Size: 3/8 in

Dim. B: Nose Diameter: 0.866 in

Length Format: Standard

Finish: Full Polish Chrome

Magnetic: Yes

SAE/Metric/Torx: SAE

UPC: 099575805462

Drive Type: 6 Point

Material: Alloy Steel