

9T2FSS

TRANSFORMER DRY 3PH 9KVA

480V-208Y/120V



Main

Product or component type	Dry Sealed Transformer
Primary Voltage	480 V delta
Full Capacity Taps	2 5 % FCBN
Secondary Voltage	208Y/120 V

Complementary

Enclosure Code	14C
Phase	3 phase
Primary to Secondary Voltage	480 V delta 208Y/120 V
Power Rating	9 kVA
Temperature rise	115 °C
Height	14.75 in (374.65 mm)
Width	19.1 in (485.14 mm)
Depth	12.25 in (311.15 mm)
Enclosure mounting	Wall mounted
Enclosure material	Stainless steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CULus CSA UL listed

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901944287
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months