

Main

Product	Transformer Disconnect
Certifications	CSA UL listed
Enclosure Type	NEMA 1 standard
Insulation Temperature	356 °F (180 °C)
Phase	1 phase
Primary Voltage	240 x 480 V
Power Rating	500 VA
Secondary Voltage	120 V
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Type	SK

Ordering and shipping details

Category	21694 - 9070 SK
Discount Schedule	CP8
GTIN	00785901099406
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------