

### Main

Product or component type	Industrial Control Transformer
Power Rating	100 VA
Primary Voltage	240 x 480 V
Secondary Voltage	24 V
Type	TF

### Complementary

Number of Phases	1 phase
Power Rating	100 VA
Primary to Secondary Voltage	240 x 480 V 24 V
Fuse type	10.3 x 38 mm CC top
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Fingersafe Cover Compatibility	FSC1

### Environment

Product certifications	CSA UL listed
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

### Ordering and shipping details

Category	16202 - 9070 TF (NOT T) 50-200VA
Discount Schedule	CP8
GTIN	00785901905219
Returnability	Yes
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

Contractual warranty

Warranty	18 months
----------	-----------