



Main

Enclosure type	Open box
Range of product	TF

Complementary

Depth	3.34 in (84.84 mm)
Device composition	Top fuse disconnecter
Electrical connection	Screw clamp terminal
Fuse type	0.41 x 1.50 in CC top
Height	4.25 in (107.95 mm)
Material	Copper winding
Mounting support	panel
Phase	1 phase
Primary voltage	380/400/415 V
Rated power in VA	100 VA
Secondary voltage	115/230 V
Temperature rise	55 °C
Width	3.38 in (85.85 mm)

Environment

Insulation temperature	221 °F (105 °C)
Product certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239 CE
Standards	UL 508 NEC 450

Ordering and shipping details

Category	16202 - 9070 TF (NOT T) 50-200VA
Discount Schedule	CP8
GTIN	00785901314158
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------