



Main

Product or component type	Industrial Control Transformer
Power Rating	50 VA
Primary Voltage	120 V
Secondary Voltage	12/24 V
Type	T

Complementary

Number of Phases	1 phase
Power Rating	50 VA
Primary to Secondary Voltage	120 V 12/24 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Height	2.58 in (65.53 mm)
Width	3 in (76.20 mm)
Depth	3.09 in (78.49 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC1

Environment

Product certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

Ordering and shipping details

Category	16200 - 9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	00785901905578
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	10 Years
----------	----------

Approximate Dimensions

