



### Main

|                           |                                |
|---------------------------|--------------------------------|
| Product or component type | Industrial Control Transformer |
| Power Rating              | 75 VA                          |
| Primary Voltage           | 120 V                          |
| Secondary Voltage         | 12/24 V                        |
| Type                      | T                              |

### Complementary

|                                |                       |
|--------------------------------|-----------------------|
| Number of Phases               | 1 phase               |
| Power Rating                   | 75 VA                 |
| Primary to Secondary Voltage   | 120 V 12/24 V         |
| Temperature rise               | 55 °C                 |
| Electrical connection          | Screw clamp terminals |
| Height                         | 2.89 in (73.41 mm)    |
| Width                          | 3.38 in (85.85 mm)    |
| Depth                          | 3.34 in (84.84 mm)    |
| Material                       | Copper winding        |
| Fingersafe Cover Compatibility | FSC1                  |

### Environment

|                        |                                                          |
|------------------------|----------------------------------------------------------|
| Product certifications | UL listed file E61239<br>CSA file LR37055 guide 184-N-90 |
| Enclosure Type         | Not rated (open device)                                  |
| Insulation temperature | 221 °F (105 °C)                                          |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 16200 - 9070 T (NOT TF) 50-200VA |
| Discount Schedule | CP8                              |
| GTIN              | 00785901905455                   |
| Returnability     | Yes                              |
| Country of origin | MX                               |

### Offer Sustainability

|                            |                                |
|----------------------------|--------------------------------|
| Sustainable offer status   | Green Premium product          |
| REACH Regulation           | REACH Declaration              |
| REACH free of SVHC         | Yes                            |
| EU RoHS Directive          | Compliant  EU RoHS Declaration |
| Toxic heavy metal free     | Yes                            |
| Mercury free               | Yes                            |
| RoHS exemption information | Yes                            |

|                          |                                                                                                                                 |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| China RoHS Regulation    | <a href="#"> China RoHS Declaration</a>         |
| Environmental Disclosure | <a href="#"> Product Environmental Profile</a> |

Contractual warranty

|          |          |
|----------|----------|
| Warranty | 10 Years |
|----------|----------|