

9070T1500D50

INDUSTRIAL CONTROL TRANSFORMER

1500VA MULTIPLE VOLTAGES



Main

Product or component type	Industrial Control Transformer
Power Rating	1500 VA 1000 VA
Primary Voltage	230/400/460/575 V 240/416/480/600 V 220/380/440/550 V 208/364/420/500 V
Secondary Voltage	99/120/130 V 91/110/120 V 85/100/110 V 95/115/125 V
Type	T

Complementary

Number of Phases	1 phase
Power Rating	1500 VA UL 1500 VA CSA 1500 VA NOM 1000 VA
Primary to Secondary Voltage	230/400/460/575 V 95/115/125 V 240/416/480/600 V 99/120/130 V 208/364/420/500 V 85/100/110 V 220/380/440/550 V 91/110/120 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	6.17 in (156.72 mm)
Width	7.06 in (179.32 mm)
Depth	7.17 in (182.12 mm)
Fingersafe Cover Compatibility	FSC23

Environment

Product certifications	CSA UL listed
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901712060
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------