

9070EL2D3

INDUSTRIAL CONTROL TRANSFORMER

100VA 208V PRIMARY WITH 610mm/24INCH LEADS



Main

Product or component type	Industrial Control Transformer
Range of product	EL

Complementary

Phase	1 phase
Rated power in VA	100 VA
Primary voltage	208 V
Secondary voltage	120 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Connector type	Lead 2001.31 ft (610 m)

Environment


Product certifications	UL listed CSA CE
NEMA degree of protection	Not rated (open device)
Insulation temperature	221 °F (105 °C)

Ordering and shipping details

Category	21691-9070 AP,E,G,H,SB
Discount Schedule	CP8
GTIN	00785901871033
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------