



### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	190/200/208/220 x 380/400/416/440 V
Full Capacity Taps	0
Secondary Voltage	110/220 V

### Complementary

Enclosure Code	7A
Phase	1 phase
Primary to Secondary Voltage	190/200/208/220 x 380/400/416/440 V 110/220 V
Power Rating	1 kVA
Temperature rise	115 °C
Height	8.13 in (206.50 mm)
Width	6.94 in (176.28 mm)
Depth	5.31 in (134.87 mm)
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel



### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	TÜV CSA CULus UL listed

### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901068730
Returnability	Yes
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------