



Main

Product	Drive Isolation Transformer
Enclosure Code	22D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
Phase	3 phase
Primary Voltage	460 V delta
Power Rating	118 kVA
Secondary Voltage	460Y/265 V
Full Capacity Taps	2 5 % 1+ 1-
Temperature Rise	150 °C
Winding Material	Aluminium

Ordering and shipping details

Category	16266 - DRIVE ISOLATION TRANSFORMERS
Discount Schedule	PE2
GTIN	00785901843313
Returnability	No
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------