



Main

Product or component type	Dry Sealed Transformer
Primary Voltage	480 V
Full Capacity Taps	2 5 % FCBN
Secondary Voltage	120/240 V

Complementary

Enclosure Code	15B
Phase	1 phase
Primary to Secondary Voltage	480 V 120/240 V
Power Rating	25 kVA
Temperature rise	115 °C
Height	20 in (508.00 mm)
Width	15 in (381.00 mm)
Depth	13.5 in (342.90 mm)
Enclosure mounting	Wall mounted
Enclosure material	Stainless steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CSA CULus UL listed

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901836896
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------