



### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	240 x 480 V
Full Capacity Taps	0
Secondary Voltage	120/240 V

### Complementary

Enclosure Code	10A
Phase	1 phase
Primary to Secondary Voltage	240 x 480 V 120/240 V
Power Rating	3 kVA
Temperature rise	115 °C
Height	266.70 mm (10.5 in)
Width	218.95 mm (8.62 in)
Depth	6.5 in (165.10 mm)
Enclosure mounting	Wall mounted
Enclosure material	Stainless steel

### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	UL listed CSA CULus

### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901169390
Returnability	No
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
<b>Contractual warranty</b>	
Warranty	18 months