

5S40FSS

TRANSFORMER DRY 1PH 5KVA

480V-120/240V

Main

Product or component type	Dry Sealed Transformer
Primary Voltage	480 V
Full Capacity Taps	2 5 % FCBN
Secondary Voltage	120/240 V

Complementary

Enclosure Code	13B
Phase	1 phase
Primary to Secondary Voltage	480 V 120/240 V
Power Rating	5 kVA
Temperature rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure mounting	Wall mounted
Enclosure material	Stainless steel



Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	UL listed CULus CSA

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901765950
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months