

# 50SV51A

## TRANSFORMER DRY 1PH .05KVA

### 600V-120/240V

#### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	600 V
Full Capacity Taps	0
Secondary Voltage	120/240 V

#### Complementary

Enclosure Code	1A
Phase	1 phase
Primary to Secondary Voltage	600 V 120/240 V
Power Rating	0.05 kVA
Temperature rise	55 °C
Height	5 in (127.00 mm)
Width	113.54 mm (4.47 in)
Depth	87.38 mm (3.44 in)
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel



#### Environment

Enclosure Type	NEMA 3R
Insulation temperature	221 °F (105 °C)
Product certifications	CULus CSA UL listed

#### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901020288
Returnability	No
Country of origin	US

#### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	 <a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------