








Main

Product	Buck and Boost Transformer
Enclosure Code	5A
Enclosure Type	NEMA 3R
Insulation Temperature	266 °F (130 °C)
Primary Voltage	120 x 240 V
Power Rating	0.5 kVA
Secondary Voltage	16/32 V
Temperature Rise	80 °C

Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901019923
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------