



### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	480 V delta
Full Capacity Taps	2 5 % FCBN
Secondary Voltage	240 V delta

### Complementary

Enclosure Code	12C
Phase	3 phase
Primary to Secondary Voltage	480 V delta 240 V delta
Power Rating	6 kVA
Temperature rise	115 °C
Height	13.5 in (342.90 mm)
Width	14.75 in (374.65 mm)
Depth	9 in (228.60 mm)
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel


### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	UL listed CSA CULus

### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901359487
Returnability	Yes
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	 <a href="#">REACH Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
<b>Contractual warranty</b>	
Warranty	18 months