

# 9070EL3D5

## INDUSTRIAL CONTROL TRANSFORMER

### 150VA MULTI-VOLTAGE WITH

### 610mm/24INCH LEADS



#### Main

Product or component type	Industrial Control Transformer
Range of product	EL

#### Complementary

Phase	1 phase
Rated power in VA	150 VA
Primary voltage	550 V 600 V 575 V
Secondary voltage	110 V 115 V 120 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Connector type	Lead 2001.31 ft (610 m)

#### Environment

Product certifications	CE CSA UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	221 °F (105 °C)

#### Ordering and shipping details

Category	21691 - 9070 AP,E,G,H,SB
Discount Schedule	CP8
GTIN	00785901674283
Returnability	No
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------