



### Main

|                           |                                |
|---------------------------|--------------------------------|
| Product or component type | Industrial Control Transformer |
| Power Rating              | 1000 VA<br>1500 VA             |
| Primary Voltage           | 460 V<br>208 V<br>230 V        |
| Secondary Voltage         | 115 V                          |
| Type                      | T                              |

### Complementary

|                                |                                                     |
|--------------------------------|-----------------------------------------------------|
| Number of Phases               | 1 phase                                             |
| Power Rating                   | 1500 VA UL<br>1500 VA CSA<br>1500 VA NOM<br>1000 VA |
| Primary to Secondary Voltage   | 208 V 115 V<br>230 V<br>460 V                       |
| Temperature rise               | 115 °C                                              |
| Electrical connection          | Screw clamp terminals                               |
| Height                         | 6.17 in (156.72 mm)                                 |
| Width                          | 7.06 in (179.32 mm)                                 |
| Depth                          | 7.17 in (182.12 mm)                                 |
| Fingersafe Cover Compatibility | FSC2                                                |

### Environment

|                        |                         |
|------------------------|-------------------------|
| Product certifications | UL listed<br>CSA        |
| Enclosure Type         | Not rated (open device) |
| Insulation temperature | 356 °F (180 °C)         |

### Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 16201 - 9070 T (NOT TF) 250-2000VA |
| Discount Schedule | CP8                                |
| GTIN              | 00785901322290                     |
| Returnability     | Yes                                |
| Country of origin | MX                                 |

### Offer Sustainability

|                          |                                |
|--------------------------|--------------------------------|
| Sustainable offer status | Green Premium product          |
| REACH Regulation         | REACH Declaration              |
| REACH free of SVHC       | Yes                            |
| EU RoHS Directive        | Compliant  EU RoHS Declaration |
| Toxic heavy metal free   | Yes                            |
| Mercury free             | Yes                            |

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| RoHS exemption information | <a href="#"> Yes</a>                            |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|